

Clara A: Clear

Clara A is a clear plastic with excellent resistance against humidity and moisture. Its key property is transparency, which sees it used in a range of applications including car headlights. The main reason why customers chose Clara A is for its transparency, but it has other advantageous properties too. It is easy to recoat and cleaning quick and easy.

Advantages

- Transparent, excellent optical clarity
- Resistant to humidity and moisture
- Easy to process and finish
- Simulates acrylic effect

Applications

- Master patterns
- Concepts and prototypes
- Fluid flow analysis
- Optical testing
- Car headlights



Clara A TECHNICAL DATA SHEET

Liquid Properties			Optical Properties		
Appearance	Clear (Customizable)		Ec	7.8-8.3 mJ/cm2	[critical exposure]
Viscosity	200~300 cps	@ 25°C (77°F)	Dp	0.17	[slope of cure-depth vs. ln(E) curve]
Density	1.10 g/cm ³	@ 25°C (77°F)			

Mechanical Properties (90 Minutes UV Postcure)		
ASTM Method	Property Description	Value
ASTM D 638	Tensile Modulus	2540-2720 MPa
ASTM D 638	Tensile Strength at Break	45-53 MPa
ASTM D 638	Elongation at Break	7-10%
ASTM D 648 @66PSI	Heat Deflection Temperature	50-55°C
ASTM D 790	Flexural Strength	60-75 Mpa
ASTM D 790	Flexural Modulus	2080-2350 Mpa
ASTM D 256	Izod Impact (Notched)	20-30 J/m
ASTM D 2240	Hardness Shore D	83

*These values may vary and depend on individual machine processing and post-curing practices.

PROTOFAB

Photoreactive Resin

Product Name :

SKU# :

Weight : 10KGS

Date of Manufacturing :

LOT# : 0007162LAR

Sealed and Stored in Dry Place at Room Temperature

Warning



1. Skin can be irritated, care should be taken at all times when handling
2. Breathing the resin can cause irritation of the skin
3. Contact with eyes is likely to cause severe irritation
4. Accidental explosion is extremely unlikely. If resin comes into contact with hands, do not touch the mouth or face
5. Liquid resin is extremely harmful to aquatic life, causing long-term damage
6. Avoid breathing in any dust / smoke/particles/resin vapour from the resin
7. Wash hands thoroughly after operation
8. Contaminated clothing should not be worn outside the working area. Always store correctly and do not dump. Dumping will cause significant environmental damage
9. Always wear protective gloves, goggles and facemask when opening
10. If spilled, wash immediately with water
11. If resin comes into contact with skin, wash thoroughly with soap, peeling skin in a shower
12. If there are signs of irritation or a rash, seek medical attention
13. If any resin enters the eyes, wash with water for several minutes. After an initial period of washing, clean eyelids, contact lenses, should carefully take them out and wash the eyes with the lowest viscosity
14. If the eyes are still irritated after washing, seek medical assistance
15. If the eyes are still irritated after washing, seek medical attention
16. Please refer to the MSDS for an approved medical treatment plan



PROTOFAB
BEYOND DIMENSIONS

PROTOFAB™
BEYOND DIMENSIONS

P : +86-592-3862946 F : +86-592-3862808 E : info@3dprotofab.com 899 Maqing Road, Haicang District, Xiamen, Fujian, China 361026

Powered by Vistar (Xiamen) Industries CO., Ltd.



Please visit us online:
www.3dprotofab.com